


## Pack à porter.

The most innovative secondary packaging **machinery**.

#### Versatile, Fast, Eco-friendly,







Sua

cpscompany.it

### Packaging material thickness:

Polyethylene (PE): Max. poly reel diameter: Max. poly reel width: from 35 to 90 My (microns) Up to 450 mm Up to 2500 mm

#### Change-over time:

Max. 25 min. - based on staff training and performances.

#### Operating panel HMI

Boom mounted rotating "HMI" enabling machine control and management. The system allows to:

- ✓ Monitor technical functions, check them and adjust them for optimum performance.
- Store format parameters in order to facilitate format changeovers.
- Detect the trouble shooting machine diagnostics.
- ✓ In English and Italian (on request in addition the customer's language)

#### Finished Bundle dimensions

Width	<b>380 mm - 850 mm</b> (with ACTIVE PULL TECH 240 mm - 850mm)
Length	380 mm – 850 mm or 1200* mm
Heigth	180 mm – 400 mm
Overlapping	50/60 mm
Pitch (length)	max 1400 mm
Handle (optional)	50/60 mm
Max Reel (width)	2500 mm



#### Product handling:

With robot ABB IRB 1200 6 axes (diapers adult & baby)

**Collating unit** (tissue roll)

#### Bundle Speed:

Up to 22 cycles/min

\*Up to **10 cycles/min** with a double stroke insertion sequence.

NB: Production speed depends on the quality of the product coming from up-stream, on packaging material characteristics and final bundle dimensions required.










/ERSATILE

SUSTRINABLE


4.0 TECHNOLOGY

# CDSH72 SUGGESTED FLOOR PLAN

Diapers



Tissue





Via A.Modigliani, 13 - 40033 Casalecchio di Reno (BO) Italy ph. +39 (051) 2986111 - cpscompany@cpscompany.it

CPS Company s.r.l.